

Rittal – The System.

Faster – better – everywhere.



SZ 2562.500

Plastic cable gland plates

State: 6/10/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2562.500 - Plastic cable gland plates with membranes

Pierce the plastic and pull through the cable. With protection category IP 65 when the cable is pulled through carefully.

Features

| | |
|--|---|
| Model No. | SZ 2562.500 |
| Product description | Just pierce the plastic with a sharp point and pull the cable through. |
| Material | Plastic to UL 94-V0 Halogen-free |
| Color | Similar to RAL 7035 |
| Note | The assignment of the flange plate size can be found on the respective housings |
| Dimensions | Width: 339 mm Depth: 149 mm Width: 13.3 " Depth: 5.87 " |
| Suitable for | Enclosure type: AE |
| Gland plate | Size: 4 |
| Protection category IP to EN 60529 | IP 65 |
| Quantity of cable entries and Ø (mm) min.-max. | 24 x 7-12 48 x 10-15 4 x 15-21 8 x 15-25 4 x 26-35 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.55 kg |
| Gross weight | 0.58 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000211 |

Features

| | |
|---------------------|---|
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Plastic cable gland plate, with membranes, WD: 339x149 mm, size: 4 |
