

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2562.500**

**Plastic cable gland plates**

State: 7/21/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2562.500 - Plastic cable gland plates with membranes

Pierce the plastic and pull through the cable. With protection category IP 65 when the cable is pulled through carefully.

## Features

Model No.	SZ 2562.500
Product description	Just pierce the plastic with a sharp point and pull the cable through.
Material	Plastic to UL 94-V0 Halogen-free
Color	Similar to RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
Dimensions	Width: 339 mm Depth: 149 mm Width: 13.3 " Depth: 5.87 "
Suitable for	Enclosure type: AE
Gland plate	Size: 4
Protection category IP to EN 60529	IP 65
Quantity of cable entries and Ø (mm) min.-max.	24 x 7-12 48 x 10-15 4 x 15-21 8 x 15-25 4 x 26-35
Packaging unit	1 pc(s).
Net weight	0.55
Gross weight	0.58
Customs tariff number	39269097
EAN	4028177325609

# Features

E-Number Sweden	E3404728
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421