

**Rittal – The System.**

Faster – better – everywhere.



# SZ 2563.100

## Metal gland plate

State: 4/4/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2563.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands with a screwdriver. Protection category IP 66 is achieved when mounting in the usual position at the bottom.

## Features

Model No.	SZ 2563.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	1 x M12 12 x M20 11 x M25 8 x M32 4 x M40
Dimensions	Width: 534 mm Depth: 149 mm Width: 21 " Depth: 5.87 "
Suitable for	Enclosure type: AE
Gland plate	Size: 5
Protection category IP to EN 60529	IP66 when mounting in the usual position at the bottom
Packaging unit	1 pc(s).
Net weight	0.96 kg
Gross weight	1.004 kg
Customs tariff number	73079100
ETIM 9	EC000211
ETIM 8	EC000211

# Features

---

ECLASS 8.0

27142421

---

Product description

SZ Metal gland plate, with metric knock-outs, WD: 534x149 mm,  
size: 5