

# Rittal – The System.

Faster – better – everywhere.



## SZ 2563.500

## Plastic cable gland plates

State: 7/11/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2563.500 - Plastic cable gland plates with membranes

Pierce the plastic and pull through the cable. With protection category IP 65 when the cable is pulled through carefully.

## Features

|  |   |
|--|---|
| Model No.                                      | SZ 2563.500   |
| Product description                            | Just pierce the plastic with a sharp point and pull the cable through.                                |
| Material                                       | Plastic to UL 94-V0<br>Halogen-free   |
| Color  | Similar to RAL 7035   |
| Note   | The assignment of the flange plate size can be found on the respective housings                       |
| Dimensions                                     | Width: 534 mm<br>Depth: 149 mm<br>Width: 21 "<br>Depth: 5.87 "  |
| Suitable for                                   | Enclosure type: AE  |
| Gland plate                                    | Size: 5   |
| Protection category IP to EN 60529             | IP 65   |
| Quantity of cable entries and Ø (mm) min.-max. | 18 x 5-9<br>16 x 7-12<br>36 x 10-15<br>6 x 15-24<br>2 x 23-30<br>2 x 26-35<br>4 x 26-54<br>1 x 50-110 |
| Packaging unit                                 | 1 pc(s).  |
| Net weight                                     | 0.86  |
| Gross weight                                   | 0.96  |

# Features

|                       |               |
|-----------------------|---------------|
| Customs tariff number | 39269097      |
| EAN                   | 4028177325616 |
| E-Number Sweden       | E3404729      |
| ETIM 9                | EC000211      |
| ETIM 8                | EC000211      |
| ECLASS 8.0            | 27142421      |