Rittal – The System.

Faster – better – everywhere.



SZ 2564.200

State: 11/16/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES


FRIEDHELM LOH GROUP

SZ 2564.200 - with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frames allow the cable gland to be installed directly (modular).







Features

Model No.	SZ 2564.200
Product description	Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frames allow the cable gland to be installed directly (modular).
Material	Plastic to UL 94-V0
Color	RAL 7035
Number of rectangular cutouts information	1x rectangular cutout takes 10 sealing inserts, small
Number of rectangular cutouts	6
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	5 x M12 4 x M16 6 x M20 5 x M25 1 x M32 1 x M40

© Rittal 2026

Features

Dimensions	Width: 534 mm Depth: 149 mm Width: 21 ″ Depth: 5.87 ″
Suitable for	Enclosure type: AX
Gland plate	Size: 4
Operating temperature range	-40 °C...80 °C -40 °F...176 °F
Protection category IP to EN 60 529	IP 66 if correctly installed
Type rating according to 508A	Type 1 Type 12
Packaging unit	1 pc(s).
Net weight	0.54 kg
Gross weight	0.573 kg
Customs tariff number	39269097
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	SZ Plastic gland plates, for AX, for cable entry, modular, pre-punched, WD: 534x149 mm, for gland plates size 4

Approvals

Approvals	UL + C-UL - FTTA