Rittal – The System.

Faster – better – everywhere.



# SZ 2564.300
# Plastic Cable Gland Plates

State: 11/10/2026 (Source: www.rittal.com/us-en)

ENCLOSURES · POWER DISTRIBUTION · CLIMATE CONTROL · IT INFRASTRUCTURE · SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SZ 2564.300 - Plastic Cable Gland Plates with diaphragms, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

## Features

| | |
|---|---|
| Model No. | SZ 2564.300 |
| Product description | Just pierce the plastic with a sharp point and pull the cable through. |
| Material | Plastic to UL 94-V0 |
| Color | Similar to RAL 7035 |
| Note | The assignment of the flange plate size can be found on the respective housings |
| Dimensions | Width: 534 mm<br>Depth: 149 mm<br>Width: 21 ″<br>Depth: 5.87 ″ |
| Suitable for | Enclosure type: AX |
| Gland plate | Size: 4 |
| Protection category IP to EN 60 529 | IP 66 if correctly installed |
| Type rating according to 508A | Type 1<br>Type 12 |
| Quantity of cable entries and Ø (mm) min.-max. | 28 x 5-11<br>48 x 10-15<br>8 x 15-25<br>2 x 19-34<br>2 x 26-35<br>2 x 26-54<br>1 x 50-110 |
| Packaging unit | 1 pc(s). |
| Net weight | 0.7 kg |

© Rittal 2026

# Features

| | |
|---|---|
| Gross weight | 0.736 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Plastic gland plates, for AX, with membranes, WD: 534x149 mm, for gland plates size 4 |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL - FTTA |