

# Rittal – The System.

Faster – better – everywhere.



## SZ 2567.200

State: 12/16/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2567.200 - with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frames allow the cable gland to be installed directly (modular).



## Features

Model No.	SZ 2567.200
Product description	Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frames allow the cable gland to be installed directly (modular).
Material	Plastic to UL 94-V0
Color	RAL 7035
Number of rectangular cutouts information	1x rectangular cutout takes 10 sealing inserts, small
Number of rectangular cutouts	6
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	4 x M12 5 x M16 5 x M20 4 x M25 3 x M32 1 x M40 1 x M50

# Features

Dimensions	Width: 436 mm Depth: 221 mm Width: 17.2 " Depth: 8.7 "
Suitable for	Enclosure type: AX
Gland plate	Size: 7
Operating temperature range	-40 °C...80 °C -40 °F...176 °F
Protection category IP to EN 60 529	IP 66 if correctly installed
Type rating according to UL 50E	Type 1 Type 12
Number knockouts	4 5 5 4 3 1 1
Metric diameter	M12 M16 M20 M25 M32 M40 M50
Packaging unit	1 pc(s).
Net weight	0.58
Gross weight	0.601
Customs tariff number	39269097
EAN	4028177938458
ETIM 9	EC000211
ETIM 8	EC000211

# Features

---

ECLASS 8.0	27142421
------------	----------

# Approvals

---

Approvals	UL + C-UL - FTTA
-----------	------------------