Rittal – The System.

Faster – better – everywhere.





SZ 2567.200

State: 10/20/2025 (Source: rittal.com/us-en)



SZ 2567.200 - with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cutouts and reinforcement frames allow the cable gland to be installed directly (modular).







Features

Model No.	SZ 2567.200
Product description	Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frames allow the cable gland to be installed directly (modular).
Material	Plastic to UL 94-V0
Color	RAL 7035
Number of rectangular cutouts information	1x rectangular cutout takes 10 sealing inserts, small
Number of rectangular cutouts	6
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	4 x M12 5 x M16 5 x M20 4 x M25 3 x M32 1 x M40 1 x M50

© Rittal 2025

Features

Dimensions	Width: 436 mm
	Depth: 221 mm
	Width: 17.2 "
	Depth: 8.7 "
Suitable for	Enclosure type: AX
Gland plate	Size: 7
Operating temperature range	-40 °C80 °C
	-40 °F176 °F
Protection category IP to EN 60 529	IP 66 if correctly installed
Type rating according to UL 50E	Type 1
	Type 12
Number knockouts	4
	5
	5
	4
	3
	1 1
Metric diameter	 M12
	M16
	M20
	M25
	M32
	M40
	M50
Packaging unit	1 pc(s).
Net weight	0.58
Gross weight	0.601
Customs tariff number	39269097
EAN	4028177938458
ETIM 9	EC000211
ETIM 8	EC000211

© Rittal 2025 3

Features

ECLASS 8.0 27142421

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025