
Rittal - The System.

Faster – better – everywhere.





SZ 2567.450

Flange plate in two parts with elastic clamping profile

State: 11/8/2025 (Source: rittal.com/us-en)



SZ 2567.450 - Flange plate in two parts with elastic clamping profile for AX

The split flange plate allows easy mounting on the housing and offers various installation options. For easy insertion of cables with or without plug connections into the housing. The special holes in the flange plate ensure automatic equipotential bonding when screwed together. Bolts, clamps or grounding cables are no longer necessary.

Features

Model No.	SZ 2567.450
Version	Two-piece
Material	Carbon steel
Color	RAL 7035
Supply includes	Assembly components
Note	The assignment of the flange plate size can be found on the respective housings
	When installing in enclosure width >760 mm, 2 PUs are required
Dimensions	Width: 436 mm
	Depth: 221 mm
	Width: 17.2 "
	Depth: 8.7 "
Suitable for	Enclosure type: AX
Suitable for Model No.	1260.000
	1339.000
	1360.000
	1376.000
	1059.000
	1091.000
	1116.000
	1261.000
Gland plate	Size: 7
Packaging unit	1 pc(s).

© Rittal 2025 2

Features

Net weight	1.4
Gross weight	1.46
PCF/VE (cradle-to-gate)	5.6 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73079100
EAN	4028177973145
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

© Rittal 2025 3