### Rittal – The System.

Faster – better – everywhere.





## AX 2571.100 Metal gland plate

State: 10/30/2025 (Source: rittal.com/us-en)



# AX 2571.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands with a screwdriver.

#### **Features**

Model No.	AX 2571.100	
Product description	Simply knock out the holes for the cable glands with a screwdriver	
Material	Carbon steel	
Color	RAL 7035	
Note	The assignment of the flange plate size can be found on the	
	respective housings	
No. of metric knockouts	2 x M12	
	2 x M16	
	9 x M20	
	5 x M25	
	1 x M32	
	1 x M40	
Dimensions	Width: 256 mm	
	Depth: 149 mm	
	Width: 10.1 "	
	Depth: 5.87 "	
Suitable for	Enclosure type: AX	
Gland plate	Size: 1	
Protection category IP to EN 60 529	IP 66 if correctly installed	
Type rating according to UL 50E	Type 1	
	Type 12K	

© Rittal 2025

#### Features

Number knockouts	2	
	2	
	9	
	5	
	1	
	1	
Metric diameter	M12	
	M16	
	M20	
	M25	
	M32	
	M40	
Packaging unit	1 pc(s).	
Net weight	0.46	
Gross weight	0.469	
PCF/VE (cradle-to-gate)	2.3 kg CO2 eq (Cat B)	
Information regarding the PCF	Category B: PCF value (cradle-to-gate) calculated approximately on	
class	the basis of the product weight and self-declared	
Customs tariff number	73079100	
EAN	4028177925304	
E-Number Sweden	E3465295	
ETIM 9	EC000211	
ETIM 8	EC000211	
ECLASS 8.0	27142421	

## Approvals

Approvals	UL + C-UL - FTTA	

© Rittal 2025 3