Rittal – The System.

Faster – better – everywhere.



# AX 2572.100

# Metal gland plate

State: 11/14/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# AX 2572.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands with a screwdriver.

## Features

| | |
|---|---|
| Model No. | AX 2572.100 |
| Product description | Simply knock out the holes for the cable glands with a screwdriver. |
| Material | Carbon steel |
| Color | RAL 7035 |
| Note | The assignment of the flange plate size can be found on the respective housings |
| No. of metric knockouts | 6 x M16<br>4 x M20<br>10 x M25<br>2 x M32<br>2 x M40 |
| Dimensions | Width: 339 mm<br>Depth: 149 mm<br>Width: 13.3 ″<br>Depth: 5.87 ″ |
| Suitable for | Enclosure type: AX |
| Gland plate | Size: 2 |
| Protection category IP to EN 60 529 | IP 66 if correctly installed |
| Type rating according to 508A | Type 1<br>Type 12K |
| Packaging unit | 1 pc(s). |
| Net weight | 0.6 kg |
| Gross weight | 0.605 kg |
| PCF/VE (cradle-to-gate) | 3 kg CO2 eq (Cat B) |

# Features

| | |
|---|---|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73079100 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |
| Product description | SZ Metal gland plate, for AX, with metric knockouts, WD: 339x149 mm, for gland plates size 2 |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL - FTTA |