### Rittal – The System.

Faster – better – everywhere.





## AX 2572.100 Metal gland plate

State: 11/4/2025 (Source: rittal.com/us-en)



# AX 2572.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands with a screwdriver.

#### **Features**

| Model No.                              | AX 2572.100   |
|--|---|
| Product description                    | Simply knock out the holes for the cable glands with a screwdrive               |
| Material                               | Carbon steel  |
| Color                                  | RAL 7035  |
| Note                                   | The assignment of the flange plate size can be found on the respective housings |
| No. of metric knockouts                | 6 x M16<br>4 x M20<br>10 x M25<br>2 x M32<br>2 x M40                            |
| Dimensions                             | Width: 339 mm  Depth: 149 mm  Width: 13.3 "  Depth: 5.87 "                      |
| Suitable for                           | Enclosure type: AX  |
| Gland plate                            | Size: 2   |
| Protection category IP to EN 60<br>529 | IP 66 if correctly installed  |
| Type rating according to UL 50E        | Type 1<br>Type 12K  |
| Number knockouts                       | 6<br>4<br>10<br>2<br>2  |

© Rittal 2025

#### Features

| M16  |
|--|
| M20  |
| M25  |
| M32  |
| M40  |
| 1 pc(s).   |
| 0.6  |
| 0.605  |
| 3 kg CO2 eq (Cat B)  |
| Category B: PCF value (cradle-to-gate) calculated approximately on |
| the basis of the product weight and self-declared                  |
| 73079100   |
| 4028177925236  |
| E3465296   |
| EC000211   |
| EC000211   |
| 27142421   |
|  |

## Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3