

# Rittal – The System.

Faster – better – everywhere.



## AX 2572.100 Metal gland plate

State: 5/21/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2572.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands with a screwdriver.

## Features

|                                    |   |
|------------------------------------|---|
| Model No.                          | AX 2572.100   |
| Product description                | Simply knock out the holes for the cable glands with a screwdriver.             |
| Material                           | Carbon steel  |
| Color                              | RAL 7035  |
| Note                               | The assignment of the flange plate size can be found on the respective housings |
| No. of metric knockouts            | 6 x M16<br>4 x M20<br>10 x M25<br>2 x M32<br>2 x M40                            |
| Dimensions                         | Width: 339 mm<br>Depth: 149 mm<br>Width: 13.3 "<br>Depth: 5.87 "                |
| Suitable for                       | Enclosure type: AX  |
| Gland plate                        | Size: 2   |
| Protection category IP to EN 60529 | IP 66 if correctly installed  |
| Type rating according to UL 50E    | Type 1<br>Type 12K  |
| Packaging unit                     | 1 pc(s).  |
| Net weight                         | 0.6 kg  |
| Gross weight                       | 0.605 kg  |
| PCF/VE (cradle-to-gate)            | 3 kg CO2 eq (Cat B)   |

# Features

---

|                                     |  |
|-------------------------------------|--|
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number               | 73079100   |
| ETIM 9                              | EC000211   |
| ETIM 8                              | EC000211   |
| ECLASS 8.0                          | 27142421   |
| Product description                 | SZ Metal gland plate, for AX, with metric knockouts, WD: 339x149 mm, for gland plates size 2                         |

---

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|