Rittal – The System.

Faster – better – everywhere.



AX 2577.100

Metal gland plate

State: 11/14/2026 (Source: www.rittal.com/us-en)

AX 2577.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands with a screwdriver.

Features

Model No.	AX 2577.100
Product description	Simply knock out the holes for the cable glands with a screwdriver.
Material	Carbon steel
Color	RAL 7035
Note	The assignment of the flange plate size can be found on the respective housings
No. of metric knockouts	6 x M12 10 x M16 8 x M20 20 x M25 4 x M32 4 x M40
Dimensions	Width: 436 mm Depth: 221 mm Width: 17.2 ˝ Depth: 8.7 ˝
Suitable for	Enclosure type: AX
Gland plate	Size: 7
Protection category IP to EN 60 529	IP 66 if correctly installed
Type rating according to 508A	Type 1 Type 12K
Packaging unit	1 pc(s).
Net weight	1.136 kg
Gross weight	1.146 kg

© Rittal 2026

Features

PCF/VE (cradle-to-gate)	5.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	73079100
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	SZ Metal gland plate, for AX, with metric knockouts, WD: 436x221 mm, for gland plates size 7

Approvals

Approvals	UL + C-UL - FTTA