

Rittal – The System.

Faster – better – everywhere.



AX 2580.007 Sealing insert

State: 7/8/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2580.007 - Sealing insert for plastic gland plate, modular and sealing frame, modular

When combined with the inlays, the slotted sealing inserts allow individual cable entry, even for pre-assembled cables.

Features

| | |
|---------------------------------|---|
| Model No. | AX 2580.007 |
| Version | Seal insert, small |
| Product description | When combined with the inlays, the slotted sealing inserts allow individual cable entry, even for pre-assembled cables. |
| Material | Plastic |
| Color | RAL 7035 |
| Type rating according to UL 50E | Type 1 Type 12 Type 4X indoor use only |
| For cable diameter | 7 mm |
| Packaging unit | 10 pc(s). |
| Net weight | 0.06 kg |
| Gross weight | 0.07 kg |
| Customs tariff number | 40082900 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |
| ECLASS 8.0 | 27149109 |
| Product description | SZ Seal inserts, for cable entry, modular, small, for cable diameter 7 mm |

Approvals

Approvals

UR + C-UR (recognized)