
Rittal – The System.

Faster - better - everywhere.





AX 2580.120 Sealing insert

State: 11/8/2025 (Source: rittal.com/us-en)



AX 2580.120 - Sealing insert for plastic gland plate, modular and sealing frame, modular

When combined with the inlays, the slotted sealing inserts allow individual cable entry, even for pre-assembled cables.

Features

Model No.	AX 2580.120
Version	Seal insert, large
Product description	When combined with the inlays, the slotted sealing inserts allow individual cable entry, even for pre-assembled cables.
Material	Plastic
Color	RAL 7035
Type rating according to UL 50E	Type 1 Type 12 Type 4X indoor use only
For cable diameter	20 mm
Packaging unit	5 pc(s).
Net weight	0.1
Gross weight	0.145
Customs tariff number	40082900
EAN	4028177939806
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Approvals

© Rittal 2025

Approvals

Approvals

UR + C-UR (recognized)

© Rittal 2025 3