

# Rittal – The System.

Faster – better – everywhere.



## AX 2580.123 Sealing insert

State: 6/6/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2580.123 - Sealing insert for plastic gland plate, modular and sealing frame, modular

When combined with the inlays, the slotted sealing inserts allow individual cable entry, even for pre-assembled cables.

## Features

Model No.	AX 2580.123
Version	Seal insert, large
Product description	When combined with the inlays, the slotted sealing inserts allow individual cable entry, even for pre-assembled cables.
Material	Plastic
Color	RAL 7035
Type rating according to UL 50E	Type 1 Type 12 Type 4X indoor use only
For cable diameter	23 mm
Packaging unit	5 pc(s).
Net weight	0.12 kg
Gross weight	0.134 kg
Customs tariff number	40082900
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Seal inserts, for cable entry, modular, large, for cable diameter 23 mm

# Approvals

---

Approvals

UR + C-UR (recognized)