

Rittal – The System.

Faster – better – everywhere.



AX 2583.100

Sealing frame, modular

State: 6/25/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2583.100 - Sealing frame, modular

For the universal use on all surfaces and walls, for feeding through pre-assembled cables and lines with a plug. Can also be mounted on 24-pole or 16-pole connector cut-outs.

Features

Model No.	AX 2583.100
Version	For 10 sealing inserts, small
Product description	For the universal use on all surfaces and walls, for feeding through pre-fabricated cables with connectors. Can also be mounted onto 24-pole or 16-pole connector cut-outs.
Material	Plastic
Color	Black
Supply includes	Sealing Frame Locking frame
Required cut-out	113.5 x 46 mm (24-pin)
Dimensions	Width: 153.08 mm Depth: 70.08 mm Width: 6.03 " Depth: 2.76 "
Protection category IP to IEC 60529	IP 66
Packaging unit	1 pc(s).
Net weight	0.12 kg
Gross weight	0.14 kg
Customs tariff number	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109

Features

Product description

SZ Sealing frame, for cable entry, modular, for 10 seal inserts or, for connector cut-outs, 24-pole

Approvals

Approvals

UR + C-UR (recognized)