Rittal – The System.

Faster - better - everywhere.





AX 2584.100 Pole clamp

State: 11/6/2025 (Source: rittal.com/us-en)



AX 2584.100 - Pole clamp for AX, KX, AX Fiberglass Reinforced Polyester, AX IT, CS wall-mounted enclosures

For reliable, convenient fastening to round or square poles.





Features

Model No.	AX 2584.100
Product description	For reliable, convenient fastening to round or square poles.
Technical specifications	For pole diameter: Ø from 40 to 170 mm
	For pole size: 🛚 from 50 to 150 mm
Material	Profile rails, clamping section: Carbon steel
	Clamping strap: Stainless steel 1.4301 (AISI 304)
Surface finish	null
Supply includes	2 profile rails, 600 mm long
	4 clamping sections
	2 clamping straps
	4 clamping brackets
	4 self-threading M10 screws for mounting on the enclosure
Note	Only suitable for housings up to 600 mm wide.

© Rittal 2025

Features

Suitable for	Enclosure type: AX
	KX
	AX plastic
	AX IT
	CS wall-mounted enclosures
	AX outdoor housing
	AE
	KL
	EB
	AX wall-mounted housing, 3-part
Type rating according to UL 50E	Type 1
	Type 3R
	Type 4
	Type 12
Packaging unit	2 pc(s).
Net weight	1.88
Gross weight	1.96
PCF/VE (cradle-to-gate)	7.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	83024900
EAN	4028177940598
E-Number Sweden	E3465274
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234

Approvals

A	III . O.III FTTA
Approvals	UL + C-UL - FTTA

© Rittal 2025 3