

# Rittal – The System.

Faster – better – everywhere.



## AX 2584.100

### Pole clamp

State: 2/1/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))



FRIEDHELM LOH GROUP

# AX 2584.100 - Pole clamp for AX, KX, AX Fiberglass Reinforced Polyester, AX IT, CS wall-mounted enclosures

For reliable, convenient fastening to round or square poles.



## Features

Model No.	AX 2584.100
Product description	For reliable, convenient fastening to round or square poles.
Technical specifications	For pole diameter: Ø from 40 to 170 mm For pole size: $\square$ from 50 to 150 mm
Material	Profile rails, clamping section: Carbon steel Clamping strap: Stainless steel 1.4301 (AISI 304)
Surface finish	Mounting angle, clamp strip: Galvanic zinc-nickel, passivated
Supply includes	2 profile rails, 600 mm long 4 clamping sections 2 clamping straps 4 clamping brackets 4 self-threading M10 screws for mounting on the enclosure
Note	Only suitable for housings up to 600 mm wide.

# Features

Suitable for	Enclosure type: AX KX AX plastic AX IT CS wall-mounted enclosures AX outdoor housing AE KL EB AX wall-mounted housing, 3-part
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
Packaging unit	2 pc(s).
Net weight	1.88
Gross weight	1.96
PCF/VE (cradle-to-gate)	7.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	83024900
EAN	4028177940598
E-Number Sweden	E3465274
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234

# Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------