

Rittal – The System.

Faster – better – everywhere.



AX 2584.100

Pole clamp

State: 6/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2584.100 - Pole clamp for AX, KX, AX Fiberglass Reinforced Polyester, AX IT, CS wall-mounted enclosures

For reliable, convenient fastening to round or square poles.



Features

Model No.	AX 2584.100
Product description	For reliable, convenient fastening to round or square poles.
Technical specifications	For pole diameter: Ø from 40 to 170 mm For pole size: □ from 50 to 150 mm
Material	Profile rails, clamping section: Carbon steel Clamping strap: Stainless steel 1.4301 (AISI 304)
Surface finish	Profile rail, clamping profile: galvanically passivated, zinc-nickel
Supply includes	2 profile rails, 600 mm long 4 clamping sections 2 clamping straps 4 clamping brackets 4 self-threading M10 screws for mounting on the enclosure
Note	Only suitable for housings up to 600 mm wide.

Features

Suitable for	Enclosure type: AX KX AX plastic AX IT CS wall-mounted enclosures AX outdoor housing AE KL EB AX wall-mounted housing, 3-part
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12
Packaging unit	2 pc(s).
Net weight	1.88 kg
Gross weight	1.96 kg
PCF/VE (cradle-to-gate)	7.3 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	83024900
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234
Product description	AX Pole clamp

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------