Rittal – The System.

Faster – better – everywhere.



TP 2694.500

TP Universal Consoles

State: 10/30/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TP 2694.500 - TP Universal Consoles

TP universal consoles, high level of stability and IP 55 protection category since the body is mostly manufactured from a single piece. Flexible front design, with option of drawers or desk attached. Easy accessibility due to separate doors. Interchangeable lock insert

Features

Model No.	TP 2694.500
Version	with short front door
Product changes	The universal console comes with the new mounting plate from the baying enclosure system VX25.
Material	Housing, base plates: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Mounting panel Base Plates
Dimensions	Width: 600 mm Height: 1,300 mm Width: 23.6 ″ Height: 51.2 ″
Dimensions of mounting plate (W x H)	499 mm x 1,196 mm 19.6 ″ x 47.1 ″
Top depth	417.5 mm 16.4 ″
Bottom depth	500 mm 19.7 ″
IK code	IK08

© Rittal 2026

Features

Note	For universal console with short front door: To maintain the protection class, the desk section must be assembled.
Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Base material	Carbon steel
Dimensions	Width: 600 mm Height: 1,300 mm Top depth: 417.5 mm Bottom depth: 500 mm Width: 23.6 ″ Height: 51.2 ″ Top depth: 16.4 ″ Bottom depth: 19.7 ″
Packaging unit	1 pc(s).
Net weight	72.2 kg
Gross weight	76 kg
Customs tariff number	94032080
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504
Product description	TP Universal console, WHD: 600x1300x500 mm, Sheet steel, with short front door

Approvals

Approvals	TÜV UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK