## Rittal – The System.

Faster – better – everywhere.





# TP 2695.500 TP Universal Consoles

State: 11/16/2025 (Source: rittal.com/us-en)



#### TP 2695.500 - TP Universal Consoles

TP universal consoles, high level of stability and IP 55 protection category since the body is mostly manufactured from a single piece. Flexible front design, with option of drawers or desk attached. Easy accessibility due to separate doors. Interchangeable lock insert

#### **Features**

Model No.	TP 2695.500
Version	with tall front door
Product modification	The universal console comes with the new mounting plate from the baying enclosure system VX25.
Material	Housing, base plates: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Mounting panel Base Plates
Dimensions	Width: 600 mm Height: 1,300 mm Width: 23.6 ″ Height: 51.2 ″
Dimensions of mounting plate (W x H)	499 mm x 1,196 mm 19.6 " x 47.1 "
Top depth	417.5 mm 16.4 ″
Bottom depth	500 mm 19.7 ″
IK code	IK08

© Rittal 2025 2

### Features

Note	For universal console with short front door: To maintain the protection class, the desk section must be assembled.
Protection category IP to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Base material	Carbon steel
Dimensions	Width: 600 mm
	Height: 1,300 mm
	Top depth: 417.5 mm
	Bottom depth: 500 mm
	Width: 23.6 "
	Height: 51.2 "
	Top depth: 16.4 ″
	Bottom depth: 19.7 "
Packaging unit	1 pc(s).
Net weight	74.1
Gross weight	78
Customs tariff number	94032080
EAN	4028177031548
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

## Approvals

Approvals	TÜV UL + C-UL (listed)
Explanations	Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3