

Rittal – The System.

Faster – better – everywhere.



FT 2731.010 Viewing Windows

State: 6/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2731.010 - Viewing Windows for AX

For external mounting on AX enclosures instead of a door and on surfaces.



Features

Model No.	FT 2731.010
Version	30 section
Product description	For mounting on AX housing instead of door and on surfaces.
Material	Frame: Aluminum, natural anodized. Glass panel: Acrylic
Supply includes	Plastic handle with lock insert # 3524 E
Protection category IP to EN 60529	IP 54
Suitable for Model No.	1010.000 1054.000 1060.000 1360.000
Suitable for	Enclosure type: AX Width: = 600 mm Height: = 600 mm Enclosure type: AX Width: = 23.6 " Height: = 23.6 "

Features

Dimensions	Width: 597 mm Height: 597 mm Depth: 36 mm Width: 23.5 " Height: 23.5 " Depth: 1.42 "
Visible area	Viewing window width: 537 mm Viewing window height: 537 mm Viewing window width: 21.1 " Viewing window height: 21.1 "
Build depth for components (max.)	32 mm 1.26 "
Packaging unit	1 pc(s).
Net weight	3.236 kg
Gross weight	3.48 kg
Customs tariff number	76101000
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204
Product description	FT Viewing window, WHD: 597x597x36 mm, for AX enclosures instead of the door and surfaces
