

Rittal – The System.

Faster – better – everywhere.



FT 2735.530 System Window

State: 8/28/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2735.530 - System Window for VX, TS, VX SE

To cover display and operating instruments or cut-outs, and provide protection from dirt and moisture as well as unauthorized access.



Features

Model No.	FT 2735.530
Version	30 section
Product description	Utilized to cover display and operating instruments or cut-outs, and provide protection from dirt and moisture as well as unauthorized access.
Material	Extruded aluminum section with die-cast zinc corner pieces and single-pane safety glass.
Surface finish	Base frame: Powder coated on the outside in RAL 7035, Hinge and lock section: Natural-anodized
Value base frame	Made from single-pane safety glass: high level of resistance to solvents and scratches, anti-static, reduced risk of injury if broken. Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm). Hinge with 180° opening angle, easily inserted.

Features

Value base frame	<p>Easily screw-fastened to the door thanks to modified dimensions (tubular door frame may be used as a drilling template).</p> <p>Readily height-adjustable.</p> <p>Stabilizes the door cut-out.</p> <p>Conceals the cut edge.</p> <p>There is no dirt on the seal, the glass is protected from being lifted out, dirt cannot drop inside, and moisture cannot run behind the window when opening.</p> <p>Frame section height 30 mm or 60 mm</p>
Protection category IP to EN 60529	IP 54
Note	<p>Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).</p> <p>Not suitable for outdoor installation</p>
Suitable for	<p>Enclosure type: VX</p> <p>TS</p> <p>VX SE</p> <p>Width: = 600 mm</p> <p>Enclosure type: VX</p> <p>TS</p> <p>VX SE</p> <p>Width: = 23.6 "</p>
Dimensions	<p>Width: 500 mm</p> <p>Height: 570 mm</p> <p>Depth: 47 mm</p> <p>Width: 19.7 "</p> <p>Height: 22.4 "</p> <p>Depth: 1.85 "</p>
Visible area	<p>Viewing window width: 363 mm</p> <p>Viewing window height: 498 mm</p> <p>Viewing window width: 14.3 "</p> <p>Viewing window height: 19.6 "</p>
Build depth for components (max.)	<p>33 mm</p> <p>1.3 "</p>
Packaging unit	1 pc(s).
Net weight	4.783

Features

Gross weight	5.06
Customs tariff number	76101000
EAN	4028177476318
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182301

Approvals

Certificates	Protection category
--------------	---------------------