

Rittal – The System.

Faster – better – everywhere.



FT 2761.010 Viewing Windows

State: 6/30/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2761.010 - Viewing Windows for AX

For external mounting on AX enclosures instead of a door and on surfaces.



Features

| | |
|------------------------------------|--|
| Model No. | FT 2761.010 |
| Version | 60 section |
| Product description | For mounting on AX housing instead of door and on surfaces. |
| Material | Frame: Aluminum, natural anodized. Glass panel: Acrylic |
| Supply includes | Plastic handle with lock insert # 3524 E |
| Protection category IP to EN 60529 | IP 54 |
| Suitable for Model No. | 1010.000 1054.000 1060.000 1360.000 |
| Suitable for | Enclosure type: AX Width: = 600 mm Height: = 600 mm Enclosure type: AX Width: = 23.6 " Height: = 23.6 " |

Features

| | |
|-----------------------------------|--|
| Dimensions | Width: 597 mm Height: 597 mm Depth: 62 mm Width: 23.5 " Height: 23.5 " Depth: 2.44 " |
| Visible area | Viewing window width: 537 mm Viewing window height: 537 mm Viewing window width: 21.1 " Viewing window height: 21.1 " |
| Build depth for components (max.) | 58 mm 2.28 " |
| Packaging unit | 1 pc(s). |
| Net weight | 4.061 kg |
| Gross weight | 4.18 kg |
| Customs tariff number | 76101000 |
| ETIM 9 | EC002527 |
| ETIM 8 | EC002527 |
| ECLASS 8.0 | 27182204 |
| Product description | FT Viewing window, WHD: 597x597x62 mm, for AX enclosures instead of the door and surfaces |
