Rittal – The System.

Faster – better – everywhere.



FT 2762.010
Viewing Windows

State: 11/12/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

FT 2762.010 - Viewing Windows for AX

For external mounting on AX enclosures instead of a door and on surfaces.





Features

Model No.	FT 2762.010
Version	60 section
Product description	For mounting on AX housing instead of door and on surfaces.
Material	Frame: Aluminum, natural anodized. Glass panel: Acrylic
Supply includes	Plastic handle with lock insert # 3524 E
Protection category IP to EN 60 529	IP 54
Suitable for Model No.	1012.000 1076.000 1376.000
Suitable for	Enclosure type: AX Width: = 600 mm Height: = 760 mm Enclosure type: AX Width: = 23.6 ″ Height: = 29.9 ″

© Rittal 2026

Features

Dimensions	Width: 597 mm Height: 757 mm Depth: 62 mm Width: 23.5 ″ Height: 29.8 ″ Depth: 2.44 ″
Visible area	Viewing window width: 537 mm Viewing window height: 697 mm Viewing window width: 21.1 ″ Viewing window height: 27.4 ″
Build depth for components (max.)	58 mm 2.28 ″
Packaging unit	1 pc(s).
Net weight	4.482 kg
Gross weight	4.682 kg
Customs tariff number	76101000
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204
Product description	FT Viewing window, WHD: 597x757x62 mm, for AX enclosures instead of the door and surfaces

© Rittal 2026