

Rittal – The System.

Faster – better – everywhere.



FT 2763.010 Viewing Windows

State: 5/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2763.010 - Viewing Windows for AX

For external mounting on AX enclosures instead of a door and on surfaces.



Features

Model No.	FT 2763.010
Version	60 section
Product description	For mounting on AX housing instead of door and on surfaces.
Material	Frame: Aluminum, natural anodized. Glass panel: Acrylic
Supply includes	Plastic handle with lock insert # 3524 E
Protection category IP to EN 60 529	IP 54
Suitable for Model No.	1050.000 1350.000 1007.000
Suitable for	Enclosure type: AX Width: = 500 mm Height: = 500 mm Enclosure type: AX Width: = 19.7 " Height: = 19.7 "

Features

Dimensions	Width: 497 mm Height: 497 mm Depth: 62 mm Width: 19.6 " Height: 19.6 " Depth: 2.44 "
Visible area	Viewing window width: 437 mm Viewing window height: 437 mm Viewing window width: 17.2 " Viewing window height: 17.2 "
Build depth for components (max.)	58 mm 2.28 "
Packaging unit	1 pc(s).
Net weight	3.44 kg
Gross weight	3.46 kg
Customs tariff number	76101000
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182204
Product description	FT Viewing window, WHD: 497x497x62 mm, for AX enclosures instead of the door and surfaces
