

# Rittal – The System.

Faster – better – everywhere.



FT 2781.000

Acrylic glazed cover

State: 2/10/2026 (Source: [ittal.com/us-en](http://ittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2781.000 - Acrylic glazed cover

To protect display and control components in standard 19" or metric dimensions.

## Features

Model No.	FT 2781.000
Version	19"
Product description	With security lock, lock no. 3524 E.
Material	Frame: Extruded aluminum sections with die-cast corner pieces Glass panel: Smoked acrylic
Supply includes	Hinges and assembly components. Incl. lock insert # 3524 E
Protection category IP to EN 60 529	IP 54
Dimensions	Width: 534 mm Height: 158 mm Depth: 47.5 mm Width: 21 " Height: 6.22 " Depth: 1.87 "
Visible area	Viewing window width: 494 mm Viewing window height: 137.5 mm Viewing window width: 19.4 " Viewing window height: 5.41 "
Build depth for components (max.)	43 mm 1.69 "
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19" Installation depth for components: 19 " Installation width for components: 19"
Packaging unit	1 pc(s).
Net weight	1.236
Gross weight	1.436

# Features

---

Customs tariff number 39205100

---

EAN 4028177032231

---

ETIM 9 EC002527

---

ETIM 8 EC002527

---

ECLASS 8.0 27182301