

# Rittal – The System.

Faster – better – everywhere.



## FT 2788.000 Acrylic glazed cover

State: 6/4/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2788.000 - Acrylic glazed cover

To protect display and control components in standard 19" or metric dimensions.

## Features

Model No.	FT 2788.000
Version	metric
Product description	With security lock, lock no. 3524 E.
Material	Frame: Extruded aluminum sections with die-cast corner pieces Glass panel: Smoked acrylic
Supply includes	Hinges and assembly components. Incl. lock insert # 3524 E
Protection category IP to EN 60529	IP 54
Dimensions	Width: 600 mm Height: 200 mm Depth: 47.5 mm Width: 23.6 " Height: 7.87 " Depth: 1.87 "
Visible area	Viewing window width: 560 mm Viewing window height: 179.5 mm Viewing window width: 22 " Viewing window height: 7.07 "
Build depth for components (max.)	43 mm 1.69 "
Packaging unit	1 pc(s).
Net weight	1.517 kg
Gross weight	1.717 kg
Customs tariff number	39205100
ETIM 9	EC002527
ETIM 8	EC002527

# Features

---

ECLASS 8.0

27182301

---

Product description

FT Acrylic glazed cover, 482.6 mm (19"), WHD: 600x200x47,5 mm