### Rittal – The System.

Faster - better - everywhere.





# FT 2789.000 Acrylic glazed cover

State: 12/14/2025 (Source: rittal.com/us-en)



## FT 2789.000 - Acrylic glazed cover

To protect display and control components in standard 19" or metric dimensions.

#### **Features**

Model No.	FT 2789.000
Version	metric
Product description	With security lock, lock no. 3524 E.
Material	Frame: Extruded aluminum sections with die-cast corner pieces Glass panel: Smoked acrylic
Supply includes	Hinges and assembly components. Incl. lock insert # 3524 E
Protection category IP to EN 60 529	IP 54
Dimensions	Width: 600 mm Height: 400 mm Depth: 47.5 mm Width: 23.6 " Height: 15.7 " Depth: 1.87 "
Visible area	Viewing window width: 560 mm Viewing window height: 379.5 mm Viewing window width: 22 " Viewing window height: 14.9 "
Build depth for components (max.)	43 mm 1.69 ″
Packaging unit	1 pc(s).
Net weight	2.46
Gross weight	2.68
Customs tariff number	39205100
EAN	4028177032378
ETIM 9	EC002527

© Rittal 2025

#### **Features**

ETIM 8	EC002527	
ECLASS 8.0	27182301	

© Rittal 2025 3