


Rittal – The System.

Faster – better – everywhere.



FT 2796.000 Acrylic glazed cover

State: 4/26/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2796.000 - Acrylic glazed cover

To protect display and control components in standard 19" or metric dimensions.

Features

Model No.	FT 2796.000
Version	19"
Product description	With security lock, lock no. 3524 E.
Material	Frame: Extruded aluminum sections with die-cast corner pieces Glass panel: Smoked acrylic
Supply includes	Hinges and assembly components. Incl. lock insert # 3524 E
Protection category IP to EN 60529	IP 54
Dimensions	Width: 534 mm Height: 425 mm Depth: 47.5 mm Width: 21 " Height: 16.7 " Depth: 1.87 "
Visible area	Viewing window width: 494 mm Viewing window height: 404.5 mm Viewing window width: 19.4 " Viewing window height: 15.9 "
Build depth for components (max.)	43 mm 1.69 "
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19" Installation depth for components: 19 " Installation width for components: 19"
Packaging unit	1 pc(s).
Net weight	2.475 kg
Gross weight	2.675 kg

Features

Customs tariff number	39205100
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182301
Product description	FT Acrylic glazed cover, 482.6 mm (19"), WHD: 534x425x47,5 mm
