

Rittal – The System.

Faster – better – everywhere.



AX 2820.101

Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm

State: 7/8/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2820.101 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm for AX

Base/plinth corner piece with a large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.

Features

Model No.	AX 2820.101
Product description	Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.
Material	Base/plinth corner piece: Carbon steel Base/plinth trim panels, front/rear: Carbon steel Corner cover: Plastic
Color	RAL 9005
Supply includes	4 x base/plinth corner pieces, 100 mm high 4 x corner covers 2 x base/plinth trim panels, front/rear, 100 mm high Assembly components
Note	Base/plinth elements are required on the sides to finish off a base/plinth unit The components of the first generation base/plinth system cannot be combined with the components of the second generation base/plinth system
Dimensions	Height: 100 mm Height: 3.94 "
Suitable for	Enclosure type: AX Width: = 1,000 mm Enclosure type: AX Width: = 39.4 "
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12

Features

Packaging unit	2 pc(s).
Net weight	4.96 kg
Customs tariff number	94039910
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003
Product description	AX Base/plinth corner pieces with base/plinth trim panels, front and rear, H: 100 mm, for W: 1000 mm

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------