Rittal - The System.

Faster – better – everywhere.





AX 2820.121

Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm

State: 11/9/2025 (Source: rittal.com/us-en)

NCLOSURES

OWER DISTRIBUTION

LIMATE CONTROL

T INFRASTRUCTURE

SOFTWARE & SERVICE

AX 2820.121 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm for AX

Base/plinth corner piece with a large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.

Features

| Model No. | AX 2820.121 |
|---------------------------------|---|
| Product description | Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover. |
| Material | Base/plinth corner piece: Carbon steel Base/plinth trim panels, front/rear: Carbon steel Corner cover: Plastic |
| Color | RAL 9005 |
| Supply includes | 4 x base/plinth corner pieces, 100 mm high 4 x corner covers 2 x base/plinth trim panels, front/rear, 100 mm high Assembly components |
| Note | Base/plinth elements are required on the sides to finish off a base/plinth unit The components of the first generation base/plinth system cannot be combined with the components of the second generation base/plinth system |
| Dimensions | Height: 100 mm Height: 3.94 ″ |
| Suitable for | Enclosure type: AX Width: = 1,200 mm Enclosure type: AX Width: = 47.2 " |
| Type rating according to UL 50E | Type 1 Type 3R Type 4 Type 12 |

© Rittal 2025

Features

| Packaging unit | 2 pc(s). |
|-----------------------|---------------|
| Net weight | 6.59 |
| Gross weight | 6.66 |
| Customs tariff number | 94039910 |
| EAN | 4028177942578 |
| ETIM 9 | EC000721 |
| ETIM 8 | EC000721 |
| ECLASS 8.0 | 27182003 |

Approvals

Approvals UL + C-UL - FTTA