

# Rittal – The System.

Faster – better – everywhere.



## AX 2820.121

Base/plinth corner pieces with  
base/plinth trim panels, front and  
rear, 100 mm

State: 2/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AX 2820.121 - Base/plinth corner pieces with base/plinth trim panels, front and rear, 100 mm for AX

Base/plinth corner piece with a large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.

## Features

Model No.	AX 2820.121
Product description	Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.
Material	Base/plinth corner piece: Carbon steel Base/plinth trim panels, front/rear: Carbon steel Corner cover: Plastic
Color	RAL 9005
Supply includes	4 x base/plinth corner pieces, 100 mm high 4 x corner covers 2 x base/plinth trim panels, front/rear, 100 mm high Assembly components
Note	Base/plinth elements are required on the sides to finish off a base/plinth unit The components of the first generation base/plinth system cannot be combined with the components of the second generation base/plinth system
Dimensions	Height: 100 mm Height: 3.94 "
Suitable for	Enclosure type: AX Width: = 1,200 mm Enclosure type: AX Width: = 47.2 "
Type rating according to UL 50E	Type 1 Type 3R Type 4 Type 12

## Features

---

Packaging unit 2 pc(s).

Net weight 6.59

Gross weight 6.66

Customs tariff number 94039910

EAN 4028177942578

ETIM 9 EC000721

ETIM 8 EC000721

ECLASS 8.0 27182003

## Approvals

---

Approvals UL + C-UL - FTTA