

Rittal – The System.

Faster – better – everywhere.



SO 2859.000 Leveling Feet

State: 6/9/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SO 2859.000 - Leveling Feet for VX, TS, VX SE in stainless steel

Mounted on enclosures, for easier floor cleaning and to compensate for floor irregularities of ± 15 mm.

Features

Model No.	SO 2859.000
Product description	Mounted on enclosures, for easier floor cleaning and to compensate for floor irregularities of ± 15 mm.
Benefits	Unimpeded access for floor cleaning, for example
Applications	Compensates for floor irregularities of max. 15 mm at installation location
Material	Stainless steel 1.4301 (AISI 304)
Supply includes	Assembly components
Max. load capacity (static) per component	350 kg 771.6 lb.
Suitable for	Enclosure type: VX TS VX SE PC
Leveling range	85 - 115 mm 3.35 - 4.53 "
Packaging unit	4 pc(s).
Net weight	3.184 kg
Customs tariff number	73181900
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Features

Product description

SO leveling foot, for VX, TS, VX SE, H: 85 - 115 mm, stainless steel,
1.4301