Rittal – The System.

Faster - better - everywhere.





SO 2890.000 Leveling Feet

State: 12/9/2025 (Source: rittal.com/us-en)



SO 2890.000 - Leveling Feet for base/plinth TS, stainless steel and base/plinth, complete, stainless steel

Mounted directly underneath the TS base/plinth and complete base/plinth. Provides stabilization on uneven floor surface and clearance at the bottom of the enclosure.

Features

Model No.	SO 2890.000
Product description	Mounted directly underneath the TS base/plinth and complete base/plinth. For unhindered access e.g. when cleaning the floor, and to even out for floor irregularities.
Benefits	Unimpeded access for floor cleaning, for example To compensate for floor irregularities
Material	Stainless steel 1.4301 (AISI 304)
Installation options	Mounted directly underneath the TS base/plinth and complete base/plinth
Max. load capacity (static) per component	400 kg 881.8 lb.
Dimensions	Thread: M16
Leveling range	45 - 120 mm 1.77 - 4.72 ˝
Packaging unit	4 pc(s).
Net weight	2.4
Gross weight	2.74
Customs tariff number	73181900
EAN	4028177034044
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

© Rittal 2025 2