

# Rittal – The System.

Faster – better – everywhere.



## SZ 2899.200 Stepped Collar

State: 4/25/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2899.200 - Stepped Collar For wall thicknesses from 1.5 to 4.5 mm

To insert cable simply cut off at the required level to match the cable diameter.



## Features

Model No.	SZ 2899.200
Product description	To insert cable, simply cut off at the required level to match the cable diameter.
Applications	For wall thicknesses from 1.5 to 4.5 mm
Material	Cover: Thermoplastic elastomer
Dimensions	Thread: M20
For wall thickness (max.)	1.5 - 4.5 mm 0.06 - 0.18 "
Protection category IP to IEC 60529	IP 54 with careful cable entry
For cable diameters	5 - 16 mm 0.2 - 0.63 "
Packaging unit	100 pc(s).
Net weight	0.2 kg
Gross weight	0.252 kg
Customs tariff number	39269097
ETIM 9	EC000879
ETIM 8	EC000879

# Features

---

ECLASS 8.0

27069216

---

Product description

SZ Stepped collar, for wall thickness from 1,5 bis 4,5 mm, for hole M20, Sealing range: 5-16 mm