

Rittal – The System.

Faster – better – everywhere.



SZ 2899.250

Stepped Collar

State: 8/4/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2899.250 - Stepped Collar For wall thicknesses from 1.5 to 4.5 mm

To insert cable simply cut off at the required level to match the cable diameter.



Features

| | |
|--------------------------------------|--|
| Model No. | SZ 2899.250 |
| Product description | To insert cable, simply cut off at the required level to match the cable diameter. |
| Applications | For wall thicknesses from 1.5 to 4.5 mm |
| Material | Cover: Thermoplastic elastomer |
| Dimensions | Thread: M25 |
| For wall thickness (max.) | 1.5 - 4.5 mm 0.06 - 0.18 " |
| Protection category IP to IEC 60 529 | IP 54 with careful cable entry |
| For cable diameters | 5 - 21 mm 0.2 - 0.83 " |
| Packaging unit | 50 pc(s). |
| Net weight | 0.1 |
| Gross weight | 0.182 |
| Customs tariff number | 39269097 |
| EAN | 4028177389618 |
| ETIM 9 | EC000879 |

Features

| | |
|------------|----------|
| ETIM 8 | EC000879 |
| ECLASS 8.0 | 27069216 |