Rittal – The System.

Faster – better – everywhere.





SZ 2899.250 Stepped Collar

State: 11/17/2025 (Source: rittal.com/us-en)



SZ 2899.250 - Stepped Collar For wall thicknesses from 1.5 to 4.5 mm

To insert cable simply cut off at the required level to match the cable diameter.



Features

Model No.	SZ 2899.250
Product description	To insert cable, simply cut off at the required level to match the cable diameter.
Applications	For wall thicknesses from 1.5 to 4.5 mm
Material	Cover: Thermoplastic elastomer
Dimensions	Thread: M25
For wall thickness (max.)	1.5 - 4.5 mm 0.06 - 0.18 ″
Protection category IP to IEC 60 529	IP 54 with careful cable entry
For cable diameters	5 - 21 mm 0.2 - 0.83 ″
Packaging unit	50 pc(s).
Net weight	0.1
Gross weight	0.182
Customs tariff number	39269097
EAN	4028177389618
ETIM 9	EC000879
	2000077

© Rittal 2025

Features

ETIM 8	EC000879	
ECLASS 8.0	27069216	

© Rittal 2025 3