

Rittal – The System.

Faster – better – everywhere.



SZ 2899.400 Stepped Collar

State: 12/13/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2899.400 - Stepped Collar For wall thicknesses from 1.5 to 4.5 mm

To insert cable simply cut off at the required level to match the cable diameter.



Features

Model No.	SZ 2899.400
Product description	To insert cable, simply cut off at the required level to match the cable diameter.
Applications	For wall thicknesses from 1.5 to 4.5 mm
Material	Cover: Thermoplastic elastomer
Dimensions	Thread: M40
For wall thickness (max.)	1.5 - 4.5 mm 0.06 - 0.18 "
Protection category IP to IEC 60 529	IP 54 with careful cable entry
For cable diameters	13 - 34 mm 0.51 - 1.34 "
Packaging unit	20 pc(s).
Net weight	0.14
Gross weight	0.155
Customs tariff number	39269097
EAN	4028177389632
ETIM 9	EC000879

Features

ETIM 8	EC000879
ECLASS 8.0	27069216