

# Rittal – The System.

Faster – better – everywhere.



## SV 3052.000 Busbar Supports

State: 4/24/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3052.000 - Busbar Supports

For 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm) busbar systems.



## Features

Model No.	SV 3052.000
Material	Fiberglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Color	RAL 7035
Number of poles	3-pole 185 mm
Suitable for busbars	50 x 10 60 x 10 80 x 10
Rated current max.	1,600 A
Note on Model No.:	The base component of the busbar support may also be used as a single-pole support.
Dimensions	Width: 24 mm Height: 515 mm Depth: 51 mm Width: 0.94 " Height: 20.3 " Depth: 2.01 "
Packaging unit	2 pc(s).
Net weight	1.26 kg
Gross weight	1.338 kg

# Features

---

Customs tariff number	85369010
ETIM 9	EC001166
ETIM 8	EC001166
ECLASS 8.0	27400607
Product description	SV Busbar support, 3-pole, 185 mm bar centre distance, for busbar WH: 50-80x10 mm

# Approvals

---

Approvals	ABS
Explanations	Declaration of conformity Declaration of conformity UK