

Rittal – The System.

Faster – better – everywhere.



SV 3055.000 Busbar Supports

State: 4/3/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3055.000 - Busbar Supports

For 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm) busbar systems.



Features

Model No.	SV 3055.000
Material	Fiberglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Color	RAL 7035
Number of poles	3-pole 150 mm
Suitable for busbars	60 x 10 80 x 10
Rated current max.	2,500 A
Dimensions	Width: 30 mm Height: 420 mm Depth: 160 mm Width: 1.18 " Height: 16.5 " Depth: 6.3 "
Packaging unit	2 pc(s).
Net weight	4.16 kg
Gross weight	4.503 kg
Customs tariff number	85469010
ETIM 9	EC001166

Features

ETIM 8	EC001166
ECLASS 8.0	27400607
Product description	SV Busbar support, 3-pole, 150 mm bar centre distance, for busbar WH: 80x10 mm

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---