

Rittal – The System.

Faster – better – everywhere.



SK 3124.010 Mains choke

State: 4/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3124.010 - Mains choke Wall-mounted Blue e+ Dynamic cooling unit

Line reactor for complying with EMC requirements according to DNV-CG-0339 Class A.

Features

Model No.	SK 3124.010
Packaging unit	1 pc(s).
Suitable for Model No.	3184.837 3185.837 3186.937 3187.937
Dimensions	Width: 40 mm Height: 44 mm Length: 76 mm Width: 1.57 " Height: 1.73 " Length: 2.99 "
Operating temperature range	0 °C...85 °C 32 °F...185 °F
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Protection category IP to IEC 60529	IP 00
Net weight	0.3 kg
Gross weight	0.382 kg
Customs tariff number	85059090
Product description	SK line reactor, for Blue e+ Dynamic wall-mounted cooling unit, 230 V, 1~, 50/60 Hz