
Rittal – The System.

Faster – better – everywhere.





SK 3148.007 Roof-mounted fan, roof vent

State: 11/18/2025 (Source: rittal.com/us-en)



SK 3148.007 - Roof-mounted fan, roof vent

Can be installed on any sufficiently large roof surface, air throughput 211.89 cfm.

Features

Model No.	SK 3148.007
Version	without fan motor
Product modification	Mounting cutouts are not compatible. Adapter frame 5050.700 is required when using the roof panel.
Material	Carbon steel, spray finished
Color	RAL 7035
Supply includes	Sealing and assembly components Drilling template
Dimensions	Width: 420 mm Height: 65 mm Depth: 340 mm Width: 16.5 " Height: 2.56 " Depth: 13.4 "
Mounting cut-out	Width of opening: 345 mm Depth of opening: 265 mm Width of opening: 13.6 " Depth of opening: 10.4 "
Protection category IP to IEC 60 529	IP 43
Note	Via additional installation of the filter holder with filter mat, a protection category of IP 44 is achieved with roof vent 3148.007.
Operating temperature range	-10 °C60 °C 14 °F140 °F
Packaging unit	1 pc(s).
Net weight	2.644
Gross weight	2.844

© Rittal 2025

Features

Customs tariff number	73269098
EAN	4028177165335
ECLASS 8.0	27180716

© Rittal 2025 3