

**Rittal – The System.**

Faster – better – everywhere.



**SK 3174.000**

**Chopped fiber filter mat**

State: 2/9/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SK 3174.000 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

## Features

Model No.	SK 3174.000
Version	for filter holders
Product description	Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibers
Note	Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
Suitable for Model No.	3175.000
Dimensions	Width: 338 mm Height: 242 mm Depth: 17 mm Width: 13.3 " Height: 9.53 " Depth: 0.67 "
Filter class	to DIN EN 779: G2
Packaging unit	3 pc(s).
Net weight	0.045
Gross weight	0.08
Customs tariff number	56039390
EAN	4028177038158
ETIM 9	EC002513
ETIM 8	EC002513

# Features

---

ECLASS 8.0

27180706

# Approvals

---

Certificates

EAC