

Rittal – The System.

Faster – better – everywhere.



SK 3174.100

Chopped fiber filter mat

State: 5/8/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3174.100 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.

Features

| | |
|--------------------------------------|---|
| Model No. | SK 3174.100 |
| Version | for roof fans |
| Product description | Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material | Chemical fibers |
| Note | Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats. |
| Suitable for Model No. | 3138.... 3139.... 3140.... |
| Dimensions | Width: 264 mm Height: 95 mm Depth: 17 mm Width: 10.4 " Height: 3.74 " Depth: 0.67 " |
| Filter class | to DIN EN 779: G3 |
| Protection category IP to IEC 60 529 | IP 55 when mounting in roof-mounted fan |
| Packaging unit | 12 pc(s). |
| Net weight | 0.012 kg |
| Gross weight | 0.1 kg |
| Customs tariff number | 56039390 |

Features

| | |
|---------------------|---|
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |
| ECLASS 8.0 | 27180706 |
| Product description | SK spare filter mat, for roof-mounted fans, for SK 3138./3139./3140. WHD: 264 x 95 x 17 mm |

Approvals

| | |
|-----------|-------------------------------|
| Approvals | CSA UR + C-UR (recognized) |
|-----------|-------------------------------|