


Rittal – The System.

Faster – better – everywhere.



SK 3201.050

Chopped fiber filter mat

State: 8/17/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3201.050 - Chopped fiber filter mat

Replacement filter mats for roof fans, filter fans or thermoelectric coolers to effectively protect control enclosure components from dirt, dust and water.



Features

Model No.	SK 3201.050
Version	for thermoelectric coolers
Product description	Made of chopped-fiber mat with a progressive construction. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibers
Note	Performance data, protection category, and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
Suitable for Model No.	3201.200 3201.300
Dimensions	Width: 90 mm Height: 106 mm Depth: 8 mm Width: 3.54 " Height: 4.17 " Depth: 0.31 "
Filter class	to DIN EN 779: G2
Packaging unit	5 pc(s).

Features

Net weight	0.01
Gross weight	0.014
Customs tariff number	56039390
EAN	4028177598676
E-Number Sweden	E3404569
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

Approvals

Certificates	EAC
--------------	-----