

Rittal – The System.

Faster – better – everywhere.



SK 3201.810

**Modular climate control concept –
climate control door VX25**

State: 1/22/2026 (Source: [ittal.com/us-en](https://www.ittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 3201.810 - Modular climate control concept – climate control door VX25 for installing cooling modules

Carbon steel climate control doors for the installation of air conditioning modules of types SK 3307.7XX to 3310.7XX.



Features

Model No.	SK 3201.810
Product description	Carbon steel climate control doors for the installation of air conditioning modules of types SK 3307.7XX to 3310.7XX. The climate control doors fit perfectly with the overall design of the enclosure.
Material	Carbon steel
Color	RAL 7035
Supply includes	Climate control door without preconfigured cooling module 180° hinges, door opening angle approx. 130°
Note on Model No.:	Suitable for VX enclosures For 1200 mm wide VX enclosures, the existing hinged door may be used, irrespective of the device position (left or right) R/h door catch
Suitable for	Enclosure type: VX: = 600 mm: = 2,000 mm Enclosure type: = 1,200 mm Enclosure type: VX: = 23.6 " = 78.7 " Enclosure type: = 47.2 "
Packaging unit	1 pc(s).
Net weight	29.2
Gross weight	30.4

Features

EAN	4028177925755
ETIM 9	EC002510
ETIM 8	EC002510
ECLASS 8.0	27180702

Approvals

Certificates	EAC
Explanations	Declaration of conformity - F-gas regulation
