

Rittal – The System.

Faster – better – everywhere.



SK 3201.990 Connection kit

State: 6/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3201.990 - Connection kit For air-water heat exchangers

For professional water supply installation and flow regulation

Features

Model No.	SK 3201.990
Product description	For professional water supply installation and flow regulation. The pressure hoses may be cut to length individually, depending on the application.
Material	Water-carrying parts EPDM/brass
Supply includes	Hose for water return Hose for water inlet including regulator valve for regulating the volumetric flow (setting range 3 to 12 l/min) Fasteners
Length	3,600 mm 142 "
Water connections	G 3/8" internal thread
Suitable for Model No.	3209.XX0 3210.XX0 3216.480 3363.XX0 3364.XX0 3373.XX0 3374.XX0 3375.XX0
Dimensions	Length: 3,600 mm Length: 142 "
Permissible operating pressure (p. max.)	1: 10 bar 14.5: 145 PSI
Packaging unit	1 pc(s).
Net weight	4 kg

Features

Gross weight	4.58 kg
Customs tariff number	85444290
ETIM 9	EC000855
ETIM 8	EC000855
ECLASS 8.0	27180704
Product description	SK Connection set, for air/water heat exchanger, G 3/8" internal thread, Length: 3600 mm
